

PH7 Portable Humidifier

7.5L/Hr



- Low pressure humidifiers work by spraying water through centrifugal force. Unlike high-pressure systems, the water is sprayed into the room in the form of a very fine mist (water droplets below 20 μ) which evaporates immediately - resulting in minimal limescale deposits.
- The humidification capacity is constant and independent of temperature and humidity level.
- Control of an external mechanical hygostat (option)
- Adjustable capacity from 1 to 7 l/h
- It reduces electrostatic charges
- IP 56

Low-pressure humidifiers are characterized by easy and cheap installation.

Technical Data

Average Power Consumption : 250 W.
Performance : 1-7.5 l/h
Air Flow : 390 m³
For the Volume/Area of the room : 1200 m³ / 500m²
Working Temperature Range : +10 C - + 35 C

Humidity Range - work : 0% RH - 100% RH
Water supply from the mains : 200... 600 kPa
Weight : 13kg
Dimensions WxDxH : 420 x 373 x 507mm

FRONT PERSPECTIVE



SIDE VIEW



BACK VIEW



GYMA INSTRUMENTS CORPORATION

457-R Boni Avenue, New Zaniga, Mandaluyong City, Philippines 1550

Tel No.: (63) 2 8470 8068 | Fax No.: (63) 2 8470 8043 | sales@gymainstruments.com | www.gymainstruments.com